

CAT. N° 0 527 18



## PANEL MOUNTING SOCKET FIXING CENTRE HYPRA - IP44 -200/250 V~ - 32 A -2P+E -PLASTIC

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,006
Weight (g)	231,00

### Product characteristics

#### LV panel mounting sockets

200 to 250 V~ 50/60 Hz - 32 A 2P+E

- To be associated with box Cat.No 0 529 40 for surface-mounting socket or Cat.No 0 529 90 for through wiring surface mounting socket
- With single fixing centres
- 32 A

### General characteristics

#### Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A

- Conform to IEC 60309-1 and IEC 60309-2
- IP 44 according to IEC 60529
- IK 09: plastic and rubber
- IK 10: metal according to IEC 62262
- Self-extinguishing:
  - 850°C (support of active parts) / 960 °C for Prinsinter)
  - 650 °C: plastic housing conform to IEC 60695-2-10
  - 50°C to + 100°C (- 20°C for Prinsinter)

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.390-391\)](#)
- [Technical page \(p.392\)](#)
- [Hypra](#)

#### Installation & technical data

- [F00138EN-03](#)

#### Installation instructions & related documents

- [2500390-03](#)

#### Environmental product profile

- [LGRP-2015-018-V1-EN](#)