

CAT. N° 0 528 63



**PANEL APPLIANCE INLET HYPRA - IP44 - 380/415 V~ - 32 A  
- 3P+E - METAL**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	2,667
Weight (g)	964,00

**Product characteristics**

**LV panel appliance inlets**

**380 to 415 V~ 50/60 Hz - 32 A 3P+E**

- To be associated with Cat.No 0 529 79 for surface appliance inlets
- Metal
- 32 A

**General characteristics**

**Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A**

- Conform to IEC 60309-1 and IEC 60309-2
- IP 44 according to IEC 60529
- IK 09: plastic and rubber
- IK 10: metal according to IEC 62262
- Self-extinguishing:
  - 850°C (support of active parts) / 960 °C for Prinsinter)
  - 650 °C: plastic housing conform to IEC 60695-2-10
  - 50°C to + 100°C (- 20°C for Prinsinter)

**Documentation**

**Catalogue pages & additional information**

- [Selection chart \(p.390-391\)](#)
- [Technical page \(p.392\)](#)
- [Hypra](#)

**Installation & technical data**

- F00138EN-03

**Installation instructions & related documents**

- [2500289-02](#)

**Agreements & certificates of conformity**

- [OC / CB-FR\\_710634](#)