

CAT. N° 0 528 72



PANEL APPLIANCE INLET HYPRA - IP44 - 200/250 V~ - 32 A - 2P+E - PLASTIC

Pack (number of units)	1
Volume (dm ³)	2,667
Weight (g)	338,00

Product characteristics

LV panel appliance inlets

200 to 250 V~ 50/60 Hz - 32 A 2P+E

- To be associated with Cat.No 0 529 79 for surface appliance inlets
- Metal
- 32 A

General characteristics

Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A

- Conform to IEC 60309-1 and IEC 60309-2
- IP 44 according to IEC 60529
- IK 09: plastic and rubber
- IK 10: metal according to IEC 62262
- Self-extinguishing:
 - 850°C (support of active parts) / 960 °C for Prinsinter)
 - 650 °C: plastic housing conform to IEC 60695-2-10
 - 50°C to + 100°C (- 20°C for Prinsinter)

Documentation

Catalogue pages & additional information

- [Selection chart \(p.390-391\)](#)
- [Technical page \(p.392\)](#)
- [Hypra](#)

Agreements & certificates of conformity

- [OC / CB-FR_710634](#)

Installation & technical data

- [F00138EN-03](#)