

CAT. N° 0 530 91


SURFACE APPLIANCE INLET HYPRA - IP66/67-55 - 380/415 V~ - 32 A - 3P+N+E

Pack (number of units)	1
Volume (dm ³)	2,667
Weight (g)	400,00

Product characteristics


LV 380 to 415 V~ 50/60 Hz

Surface appliance inlets

- 32 A

General characteristics
Hypra IP 66/67-55 plastic - increased safety - LV 16 to 125 A

- Conform to IEC 60309-1 and IEC 60309-2
- IP according to IEC 60529
- IK 09: Plastic
- Self-extinguishing: 850°C (support of active parts) / 650°C (plastic housing)

Documentation
 **Catalogue pages & additional information**

- [Selection chart \(p.393\)](#)
- [Hypra](#)

 **Agreements & certificates of conformity**

- [OC / CB-FR_710634](#)

 **Installation & technical data**

- [F00130EN-06](#)