

CAT. N° 0 576 76



PANEL MOUNTING SOCKET P17 - IP54 - IK09 250 V~ - 2P+E SHUTTERS - BLUE

Pack (number of units)	20
Volume (dm ³)	9,294
Weight (g)	1 755,00

Product characteristics

Panel mounting sockets

- Domestic pin configuration German standard sockets
- IP 54 cover closed - IP 44 connected
- IK 09 according to IEC 62262 and EN 62262
- 2P+E 250 V~
- Material: plastic
- Self-extinguishing: 850 °C

Panel mounting sockets

- Can be fixed on pre-cut or plain faceplate for combined units, flush-mounting boxes Cat.Nos 0 577 21/22
- Blue panel mounting sockets with shutters

General characteristics

P 17 Tempra - domestic pin configuration 16 A - 250 V~

Documentation

Catalogue pages & additional information

- [Description page \(p.383\)](#)
- [Selection chart \(p.386-387\)](#)
- [Technical page \(p.388\)](#)
- [P 17 Tempra Pro](#)

Installation & technical data

- [F00390EN-05](#)