

REF . 0 577 14



FACEPLATE FOR COMBINED UNIT P17 - 3 SOCKETS 16 A



Emballage (nombre number of units)	4
Volume (dm ³)	8
Poids (g)	1 205,00

Caractéristiques du produit

Combined units height 280 mm to 501 mm

280 x 125 mm faceplate

- 3 sockets 16 A
- Supplied with blanking plate
- To be fixed horizontally except 16 A domestic pin sockets, vertically (IP 44 - connected)

Caractéristiques générales

P17 Tempra combined units to be composed

- IK 08 according to IEC 62262
- Self-extinguishing: 650 °C
- Max. IP 66

Documentation associée



Catalogue pages & additional information

- [Selection chart \(p.386-387\)](#)
- [Technical page \(p.388\)](#)



Installation & technical data

- [F00140EN-05](#)



Installation instructions & related documents

- [2500410-01](#)