

REF . 0 589 38

**BASE UP TO 2 SOCKETS FOR COMBINED UNIT P17 - 16 A  
-371 X 125 MM**

Emballage (nombre number of units )	1
Volume (dm <sup>3</sup> )	11
Poids (g)	840,00

**Caractéristiques du produit****Combined units height 220 mm to 441 mm****Base for 220 x 125 mm faceplates - max. IP 66**

- Base up to 2 sockets 16 A
- Rail 5 modules 17.5 mm
- External dimensions (Height x Width) : 371 x 125 mm

**Caractéristiques générales****P17 Tempra combined units to be composed**

- IK 08 according to IEC 62262
- Self-extinguishing: 650 °C
- Max. IP 66

**Documentation associée****Catalogue pages & additional information**

- [Selection chart \(p.386-387\)](#)
- [Technical page \(p.388\)](#)

**Installation & technical data**

- [F00140EN-05](#)