

REF . 0 601 98

**CEILING ROSE WITH PLUG-IN CONNECTION - 4 PIN WHITE  
- FIRE RESISTANT UL94 VO**

Emballage (nombre number of units )	O/R
Volume (dm <sup>3</sup> )	O/R
Poids (g)	O/R

**Caractéristiques du produit****Ceiling roses**

- Terminals: 5 x 0.75 mm<sup>2</sup>, 3 x 1.5 mm<sup>2</sup>, 2 x 2.5 mm<sup>2</sup>, 2 x 4 mm<sup>2</sup>
- Strong load grips support: up to 5 kg

**With plug-in connection**

- 4 pin white. Fire resistant UL94Vo

**Caractéristiques générales****Lighting equipment****Documentation associée****Catalogue pages & additional information**

- [Description page \(p.644\)](#)

**Installation & technical data**

- [F02567EN-01](#)

**Installation instructions & related documents**

- [LE10739AB](#)