

CAT. N° 0 660 02



## EMERGENCY LIGHTING LUMINAIRE S8 - 8 W COMBINED - 1H - 140 LM

Pack (number of units)	1
Volume (dm <sup>3</sup> )	3,007
Weight (g)	1 026,00

### Product characteristics

#### 8 W fluorescent non-maintained, maintained and combined units

- Certified to IEC 60598-2-22 and EN 60598-2-22 standards
- IP 42 - Class II
- Power supply: 230 V +/- 10% - 50/60 Hz
- Lamp and emergency operation test with a push-button
- Ni-Cd batteries
- Recharge time: 24 hours
- High capacity screw terminals: 2 x 2.5 mm<sup>2</sup>
- Charge monitor with a green LED

#### 1 h duration - 140 lm

- Combined - 140 lm - 1h (2 x 8 W)

### General characteristics

#### S8 - indoor standard self-contained emergency lighting luminaires 8 W fluorescent - BS compliant

- Can be equipped with metallic protection grid Cat.No 0 626 91

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.679\)](#)
- [Description page \(p.687\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)

#### Agreements & certificates of conformity

- [OC / CB - ES1953-M3](#)

#### Installation instructions & related documents

- [LE08468AA](#)