

CAT. N° 0 695 22



AUTOMATIC SWITCH PLEKO WITH NEUTRAL - 3-WIRE - IP55 IK07 - 230 V~ - 50 HZ - GREY/WHITE

Pack (number of units)	1
Volume (dm ³)	0,677
Weight (g)	102,00

Product characteristics

Automatic switches 230 V~ - 50 Hz

- IP 55 - IK 07
- Infrared detection
- Detection distance: 8 m
- Detection angle 120°
- Adjustable time delay: 10 s to 10 min
- Light level threshold: 5 to 1275 lux
- Should preferably be installed in box depth 50 mm

With neutral, 3-wire

- For controlling lamps:
 - LEDs: 0 to 250 W
 - compact fluorescent: 0 to 250 W
 - LEDs, CFLs with ferromagnetic or electronic ballast: 0 to 250 VA
 - halogen with ferromagnetic or electronic ballast: 0 to 500 VA ; fluorescent tube with ferromagnetic or electronic ballast: 0 to 5 x (2 x 36 W)
- 230 V halogen, incandescent: 0 to 1000 W
- Option of connecting several automatic switches in parallel
- Consumption on standby: 0.035 W
- Grey/White

General characteristics

Plexo™ mechanisms - switches, push-buttons and automatic switches IP 55

- Mechanisms supplied with cover plate
- Installation with surface-mounting boxes or flush-mounting support frames
- Automatic terminals

Documentation

Catalogue pages & additional information

- [Description page \(p.604\)](#)

Installation & technical data

- [F00339EN-06](#)

Installation instructions & related documents

- [LE09431AA_1](#)