

CAT. N° 0 767 20



## ELECTRONIC ROOM THERMOSTAT MOSAIC - 2 MODULES - WHITE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,547
Weight (g)	95,00

### Product characteristics

#### Room thermostats

- Power supply 230 V~ - 50/60 Hz
- Suitable for regulation of ceiling panel heating and direct floor heating

#### Electronic

- Alternatively for cooling systems
- Adjustment range from 10 °C to 30 °C
- Frost protection 7 °C
- Adjustment accuracy +/- 0.5 °C (category B)
- One output by non-powered contact
- Pushbutton on front face for selecting the operating mode (off, switch off when temperature falls or rises)
- Adjustable brightness of LEDs
- LV use. Breaking capacity:
  - 8 A / 250 V~ - resistive circuit
  - 2 A / 250 V~ - inductive circuit
- ELV use. Breaking capacity from 1 mA min. to 500 mA max. 12 to 48 V~ / 12 to 24 VDC
- 2 modules
- White

### General characteristics

#### Mosaic™ Programme mechanisms - heating, temperature regulation

- Fast connection via automatic terminals, no tool required

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.884\)](#)



#### Installation & technical data

- [F01857EN-01](#)



#### Installation instructions & related documents

- [292249-05](#)