

CAT. N° 0 775 22



**PROXIMITY MCB MOSAIC - SINGLE POLE - WITH NEUTRAL 230 V~ - 16 A - 2 MODULES - WHITE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,188
Weight (g)	63,00

**Product characteristics**

**Proximity MCBs**

- Used for local protection of part of a circuit against overloads and short circuits
- Used in addition to the main protection device
- Due to its proximity to the user and its discrimination with the main protection device, the restart can be immediate
- 2 modules

**Single pole thermal magnetic MCB + Neutral 230 V~**

- Can also be used as a local consumption limiter (depending on its rating)
- Breaking capacity: 3000 A - NF C 61-410 (10/16 A), 1500 A - NF C 61-410 (6 A)
- White
- 16 A

**General characteristics**

**Mosaic™ Programme mechanisms - voltage surge protector, replacement module, buzzers, bells, blanking plates, cable outlets and proximity MCBs**

**Documentation**

 **Catalogue pages & additional information**

- [Description page \(p.890\)](#)
- [Mosaic™ Programme mechanisms - proximity MCBs](#)
- [Mosaic™ Programme mechanisms - proximity MCBs](#)

 **Agreements & certificates of conformity**

- [IMQ - CA03.00605](#)
- [OC / CB - 8320-M1](#)