

CAT. N° 0 778 11

**2-WAY SWITCH SOLIROC - 10 AX 250 V~ - IP55**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,68
Weight (g)	192,00

**Product characteristics****Switches 10 AX - 250 V~**

- 2-way switch

**General characteristics****Soliroc™ - control mechanisms IK 10**

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings
- High resistance to IK 10 impacts and humidity
- 4 fixing points by plugging the plate directly on the wall and 4 blanking plates to be force-mounted on the plate (can only be removed by drilling)
- Mechanisms supplied with cover plates, to be equipped with support frames and plates

**Documentation****Catalogue pages & additional information**

- [Description page \(p.610\)](#)

**Agreements & certificates of conformity**

- [NF - NF012\\_1023](#)
- [OC / CB - FR\\_707077](#)

**Installation & technical data**

- [F00997EN-05](#)