

CAT. N° 0 778 24



AUTOMATIC SWITCH PLEXO WITH NEUTRAL - 3-WIRE - IP55 IK10

Pack (number of units)	1
Volume (dm ³)	0,677
Weight (g)	180,00

Product characteristics

Automatic switches - IK 10 - IP 55

- Infrared detection
- Detection distance: 8 m
- Detection angle: 120°
- Light level threshold: 5 to 1275 lux
- Adjustable time delay: 10 s to 10 min
- Should preferably be installed in box depth 50 mm

With neutral, 3-wire

- For controlling lamps :
- LEDs: 0 to 250 W
- compact fluorescent: 0 to 250 W
- LEDs, CFLs with ferromagnetic or electronic ballast: 0 to 250 V~
- halogen with ferromagnetic or electronic ballast: 0 to 500 V~
- fluorescent tube with ferromagnetic or electronic ballast: 0 to 5 x (2 x 36 W)
- 230 V halogen, incandescent: 0 to 1000 W
- Option of connecting several automatic switches in parallel
- Consumption on standby: 0.035 W

General characteristics

Soliroc™ - control mechanisms IK 10

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings
- High resistance to IK 10 impacts and humidity
- 4 fixing points by plugging the plate directly on the wall and 4 blanking plates to be force-mounted on the plate (can only be removed by drilling)
- Mechanisms supplied with cover plates, to be equipped with support frames and plates

Documentation



Catalogue pages & additional information

- [Description page \(p.610\)](#)



Installation & technical data

- [F00996EN-04](#)



Installation instructions & related documents

- [LE01209AC](#)