

CAT. N° 0 778 74



## 2-POSITION KEYSWITCH SOLIROC - 6 A 230 V - IP54 - 2 NO CONTACTS

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,68
Weight (g)	185,00

### Product characteristics

#### Keyswitches - IK 10 - IP 54

- To be equipped with European key barrel Cat.No 0 697 95
- 2-position keyswitch
- 1 contact - 2 poles - 6 A – 230 V
- Key extracted in central position without changing the status of the contacts (on/off)

### General characteristics

#### Soliroc™ - control mechanisms IK 10

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings
- High resistance to IK 10 impacts and humidity
- 4 fixing points by plugging the plate directly on the wall and 4 blanking plates to be force-mounted on the plate (can only be removed by drilling)
- Mechanisms supplied with cover plates, to be equipped with support frames and plates

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.611\)](#)

#### Installation & technical data

- F00999EN-04

#### Installation instructions & related documents

- [LE01207AC](#)