

CAT. N° 0 778 75



### 3-POSITION KEY-OPERATED PUSHBUTTON SOLIROC - 6 A-230 V - IP54 - WITH OFF POSITION

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 0,68   |
| Weight (g)                | 181,00 |

#### Product characteristics

##### Keyswitches - IK 10 - IP 54

- To be equipped with European key barrel Cat.No 0 697 95
- 3-position key-operated push-button
- Changeover switch with off position - 6 A - 230 V
- Key extracted in off position

#### General characteristics

##### Soliroc™ - control mechanisms IK 10

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings
- High resistance to IK 10 impacts and humidity
- 4 fixing points by plugging the plate directly on the wall and 4 blanking plates to be force-mounted on the plate (can only be removed by drilling)
- Mechanisms supplied with cover plates, to be equipped with support frames and plates

#### Documentation

##### Catalogue pages & additional information

- [Description page \(p.611\)](#)

##### Installation & technical data

- F00999EN-04

##### Installation instructions & related documents

- [LE01207AC](#)