

CAT. N° 0 784 05



DIMMER SWITCH MOSAIC -600 W- STATUS MEMORY FUNCTION - 2 MODULES - WHITE

Pack (number of units)	1
Volume (dm ³)	0,536
Weight (g)	87,00

Product characteristics

Dimmer switches 110-230 V~ 50 Hz

- Can be remotely controlled via non-illuminated pushbuttons, with each pushbutton able to perform the dimming function
- When switched on, lighten at the level set before last switched off
- For installation in flush-mounting box depth 40 mm min

Leading edge dimmer, without neutral

- For the following types of lamps:
 - halogen 230 V and incandescent: 40 W to 600 W
 - halogen with ferromagnetic or electronic type L transformer: 40 VA to 600 VA
- 2 modules
- White

General characteristics

Mosaic™ Programme mechanisms - dimming control

Documentation

Catalogue pages & additional information

- [Description page \(p.881\)](#)
- [Technical page \(p.882\)](#)

Installation & technical data

- [F00483EN-01](#)

Installation instructions & related documents

- [0064JC3-01](#)

Agreements & certificates of conformity

- [NF - NF012_1945](#)
- [OC / CB - 630164B/A1](#)