

CAT. N° 0 786 24



RJ45 SOCKET MOSAIC - REAR PLUGGABLE - CATEGORY 5E UTP - 8 CONTACTS - ALUMINIUM

Pack (number of units)	10
Volume (dm ³)	2,189
Weight (g)	225,00

Product characteristics

Rear pluggable RJ 45 sockets

- For use with area distribution boxes system
- Connection to boxes via RJ 45-RJ 45 cords
- Used to create Cat. 6A, 6 and 5e links in accordance with standards ISO 11801 ed.2.0, EN 50173-1 and EIA/TIA 568 B2
- Multi-directional cable entry
- Can be installed in all supports minimum depth 40 mm
- 2 modules

Cat. 5e UTP

- 8 contacts
- Aluminium

General characteristics

Mosaic™ Programme mechanisms - rear pluggable RJ 45 sockets and switches

Documentation



Catalogue pages & additional information

- [Description page \(p.739\)](#)
- [Selection chart \(p.840\)](#)
- [Description page \(p.893\)](#)



Installation instructions & related documents

- [LE00016AC](#)