

CAT. N° 0 787 94



TV STAR SOCKET MOSAIC - TV-R-SAT - SAT - 2 MODULES - WHITE

Pack (number of units)	10
Volume (dm ³)	2,283
Weight (g)	844,00

Product characteristics

Multi TV star sockets

TV-R-SAT - SAT 2 modules

- White
- (In 1 TV-R-SAT / In 2 SAT 2)
- Low attenuation: 1.5 dB
- Can be installed in receptacles for floor sockets

General characteristics

Mosaic™ Programme mechanisms - television sockets

- For DVBT, Cablecast and satellite installation
- UHD TV compatible
- Class A shielded star sockets LTE Ready (4G protected)
- Recommended coaxial cable: 17 VATC
- Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch)
- Visual checking of the connection
- Meet EN 50083-4 and EN 50083-2 European directive
- TV: male connector (Ø9.5 mm) - 5-68 / 120-862 MHz
- R: female connector (Ø9.5 mm) - 87.5-108 MHz
- SAT: "F type" connector - 950-2400 MHz

Documentation



Catalogue pages & additional information

- [Description page \(p.894\)](#)
- [Valena, Synergy and MosaicTMPprogramme - TV sockets](#)



Installation instructions & related documents

- [LE08365AA](#)