

CAT. N° 0 787 95



## TV STAR SOCKET MOSAIC - TV-SAT - 1 MODULE - WHITE

Pack (number of units)	5
Volume (dm <sup>3</sup> )	0,798
Weight (g)	239,00

### Product characteristics

#### Multi TV star sockets

##### TV-SAT - 1 module

- White
- Low attenuation: 1 dB

### General characteristics

#### Mosaic™ Programme mechanisms - television sockets

- For DVBT, Cablecast and satellite installation
- UHD TV compatible
- Class A shielded star sockets LTE Ready (4G protected)
- Recommended coaxial cable: 17 VATC
- Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch)
- Visual checking of the connection
- Meet EN 50083-4 and EN 50083-2 European directive
- TV: male connector (Ø9.5 mm) - 5-68 / 120-862 MHz
- R: female connector (Ø9.5 mm) - 87.5-108 MHz
- SAT: "F type" connector - 950-2400 MHz

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.894\)](#)
- [Valena, Synergy and MosaicTMPogramme - TV sockets](#)

#### Installation & technical data

- [F03269EN-00](#)

#### Installation instructions & related documents

- [LE08365AA](#)