

REF . 0 792 58



3-WIRE MOTION SENSOR MOSAIC - WITH NEUTRAL - IR DETECTION - 2000 W - ALU



| | |
|-------------------------------------|-------|
| Emballage (nombre number of units) | 1 |
| Volume (dm ³) | 0,237 |
| Poids (g) | 70,00 |

Caractéristiques du produit

3-wire motion sensors, with neutral

IR detection - 2000 W

- Checks the light level continuously and not only at the time of detection
- Accepted power by lamp type :
 - LEDs: 0 to 250 W
 - Compact fluorescent: 0 to 250 W
 - LEDs, CFLs, Halogen, fluo tubes with ferromagnetic or electronic transformer: 0 to 1000 VA
 - Halogen 230 V, incandescent: 0 to 2000 W
- Up to 10 sensors can be connected in parallel
- Additional remote manual control possible with push button
- Time delay setting from 5s to 30 min
- Light level threshold setting from 5 lux to 1275 lux
- Standby consumption : 0.2 W
- Alu

Caractéristiques générales

Mosaic™ Programme mechanisms - motion and presence sensors

- All sensors are compatible with any lamp - Detection field: 120°
- Detection range: 8 m
- Recommended installation height: 1.20 m
- Integrated self-protection against overloads and short-circuits.
- 2 modules

Documentation associée

Catalogue pages & additional information

- [Description page \(p.880\)](#)
- [Technical page \(p.882\)](#)

Installation & technical data

- [S000074408EN-05](#)

Installation instructions & related documents

- [LE04334AB](#)

Agreements & certificates of conformity

- [OC / CB-645761D](#)