

CAT. N° 0 802 52

**SUPPORT MOSAIC - WITH SITE PROTECTION - FOR 4, 5 OR 2 X 2 HORIZONTAL/VERTICAL MODULES**

Pack (number of units)	10
Volume (dm ³)	2,556
Weight (g)	671,00

Product characteristics**Supports with site protection**

- For 4, 5 or 2 x 2 modules, horizontal or vertical

General characteristics**Mosaic™ Programme supports****Documentation****Catalogue pages & additional information**

- [Selection chart \(p.900-901\)](#)
- [Description page \(p.906\)](#)

**Installation & technical data**

- [F00440EN-01](#)

CAT. N° 0 802 52

 **Agreements & certificates of conformity**

- [NF-NF012_2666](#)
- [NF-NF012_1023](#)
- [MEEI-UP 69258630 0001](#)
- [NF-NF012_1362](#)
- [OC / CB-FR_700177/A1](#)
- [OC / CB-FR_630163B/A1](#)
- [OC / CB-FR_708376](#)
- [OC / CB-FR_709693](#)
- [NF-NF012_2513](#)
- [OC / CB-569889/A1](#)
- [OC / CB-FR_707308/A1](#)
- [NF-NF012_1947](#)
- [IRAM-DC-E-E100-003](#)
- [OC / CB-620080](#)
- [OC / CB-FR_701873](#)
- [OC / CB-619737](#)
- [NF-NF012_2201/A1](#)
- [OC / CB-FR_709703](#)
- [OC / CB-FR_707077](#)
- [OC / CB-FR_707532](#)
- [NF-NF012_1945](#)
- [B](#)
- [OC / CB-FR_705591/A2](#)
- [B](#)
- [OC / CB-630164B/A1](#)
- [OC / CB-FR_709181](#)

 **Environmental product profile**

- [LGRP-01120-V01](#)
- [LGRP-01211-V01](#)
- [LGRP-01279-V01](#)