

CAT. N° 0 920 03



ROUND PLE XO BOXES WITH 4 DIRECT ENTRY MEMBRANE GLANDS - IP55 IK07 - Ø70 HEIGHT 45 - WHITE RAL 9010

Pack (number of units)	20
Volume (dm ³)	12
Weight (g)	1 194,00

Product characteristics

Round boxes

- Clippable covers
- 4 membrane glands
- Accepted cable and tube Ø: 4 to 20 mm
- White RAL 9010
- Ø70 - height 45

General characteristics

Plexo™ boxes IP 55 - IK 07 - with direct entry membrane glands - 650° C

- IP 55 - IK 07
- Resistance to incandescent wire 650°C
- For use as junction boxes in any type of normal installation circuit
- Operating temperature: -25 to +40°C
- Interchangeable membrane glands with direct entries for IRL tubes up to Ø16 and R02V cables, with marked cut-out for IRL tube Ø greater than 16
- Captive cover with tie. Space for marking on both sides of the cover. Fixing with vertical level adjustment. Class II is ensured by protective caps (supplied) for the fixing screws
- Boxes without halogenated flame retardants (European Directive RoHS 2002/95/EC)

Documentation

Catalogue pages & additional information

- [Description page \(p.613\)](#)
- [Technical page \(p.616-617\)](#)

Agreements & certificates of conformity

- [OC / CB - 665305](#)

Installation & technical data

- [F01039EN-01](#)