

CAT. N° 0 920 04



## COMPACT PLEKO BOX WITH 10 MEMBRANE GLANDS - IP55 IK07 - 80X43X34MM - GREY RAL 7035

Pack (number of units)	200
Volume (dm <sup>3</sup> )	41,4
Weight (g)	4 863,00

### Product characteristics

#### Compact box

80 x 43 x 34 mm

- Grey
- RAL 7035
- Ideal for confined spaces
- Clippable covers
- 10 membrane glands
- Accepted cable and tube Ø: 7 to 16 mm

### General characteristics

#### Plexo™ boxes IP 55 - IK 07 - with direct entry membrane glands - 650° C

- IP 55 - IK 07
- Resistance to incandescent wire 650°C
- For use as junction boxes in any type of normal installation circuit
- Operating temperature: -25 to +40°C
- Interchangeable membrane glands with direct entries for IRL tubes up to Ø16 and R02V cables, with marked cut-out for IRL tube Ø greater than 16
- Captive cover with tie. Space for marking on both sides of the cover. Fixing with vertical level adjustment. Class II is ensured by protective caps (supplied) for the fixing screws
- Boxes without halogenated flame retardants (European Directive RoHS 2002/95/EC)

### Documentation



#### Installation & technical data

- F02789EN-00