

CAT. N° 0 920 11



## SQUARE PLEXO BOX WITH 7 DIRECT ENTRY MEMBRANE GLANDS AND SMOOTH FACES - IP55 IK07 - 80X80X45 MM - GREY RAL 7035

Pack (number of units)	50
Volume (dm <sup>3</sup> )	32,4
Weight (g)	3 510,00

### Product characteristics

#### Square boxes

- Can be fixed using a tool such as a Pulsa 700 E nail gun
- 7 membrane glands

#### 80 x 80 x 45 mm

- Clippable covers
- Fixed using 2 internal points (screws with max. Ø 5 mm) or on plug Cat.No. 0 319 57
- Grey RAL 7035
- Smooth faces

### General characteristics

#### Plexo™ boxes IP 55 - IK 07 - with direct entry membrane glands - 650° C

- IP 55 - IK 07
- Resistance to incandescent wire 650°C
- For use as junction boxes in any type of normal installation circuit
- Operating temperature: -25 to +40°C
- Interchangeable membrane glands with direct entries for IRL tubes up to Ø16 and R02V cables, with marked cut-out for IRL tube Ø greater than 16
- Captive cover with tie. Space for marking on both sides of the cover. Fixing with vertical level adjustment. Class II is ensured by protective caps (supplied) for the fixing screws
- Boxes without halogenated flame retardants (European Directive RoHS 2002/95/EC)

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.613\)](#)
- [Technical page \(p.616-617\)](#)

#### Installation & technical data

- [F01039EN-02](#)