

CAT. N° 0 920 22



SQUARE PLEEXO BOX WITH 7 DIRECT ENTRY MEMBRANE GLANDS - IP55 IK07 - 105X105X55 MM - GREY RAL 7035

Pack (number of units)	50
Volume (dm ³)	62,119
Weight (g)	8 015,00

Product characteristics

Square boxes

- Can be fixed using a tool such as a Pulsa 700 E nail gun
- 7 membrane glands

105 x 105 x 55 mm

- Grey RAL 7035
- Accepted cable and tube Ø: 4 to 25 mm
- Cover closed with a 1/4 turn

General characteristics

Plexo™ boxes IP 55 - IK 07 - with direct entry membrane glands - 650° C

- IP 55 - IK 07
- Resistance to incandescent wire 650°C
- For use as junction boxes in any type of normal installation circuit
- Operating temperature: -25 to +40°C
- Interchangeable membrane glands with direct entries for IRL tubes up to Ø16 and R02V cables, with marked cut-out for IRL tube Ø greater than 16
- Captive cover with tie. Space for marking on both sides of the cover. Fixing with vertical level adjustment. Class II is ensured by protective caps (supplied) for the fixing screws
- Boxes without halogenated flame retardants (European Directive RoHS 2002/95/EC)

Documentation

Catalogue pages & additional information

- [Description page \(p.613\)](#)
- [Technical page \(p.616-617\)](#)

Environmental product profile

- [LGRP-01284-V01](#)

Installation & technical data

- [F01039EN-02](#)
- [FT0746-CABLO-IBP-BP-105](#)