

CAT. N° 0 920 25



SQUARE PLEEXO BOX WITH 7 DIRECT ENTRY MEMBRANE GLANDS - IP55 IK07 - 105X105X55 MM - GREY/RED RAL 7035/3000

Pack (number of units)	10
Volume (dm ³)	17
Weight (g)	1 874,00

Product characteristics

Square boxes

- Grey/red RAL 7037/3000

105 x 105 x 55 mm

- Cover closed with a 1/4 turn
- Fixed using 2 internal points (screws with max. Ø 5 mm) or 3 points outside the wiring space (screws with max. Ø 4 mm)
- 7 membrane glands (Cat.No 0 919 01)
- Accepted cable and tube Ø : 4 to 25 mm

General characteristics

Plexo™ boxes IP 55 - IK 07 - with direct entry membrane glands - 960 °C

- Resistance to incandescent wire: 960°C
- Junction boxes for safety circuit installations in buildings open to the public and work premises
- Operating temperature: -25 to +40°C
- Interchangeable membrane glands with direct entry for IRL tubes up to Ø16 and R02V cables. Marked cut-out for IRL tubes Ø greater than 16
- Captive cover with clippable tie between box and cover
- Space for marking on both sides of the cover of 80 x 80 and 105 x 105 boxes
- Fixing with vertical level adjustment
- Class II is ensured by protective caps (supplied) for the fixing screws

Documentation



Catalogue pages & additional information

- [Description page \(p.614\)](#)
- [Technical page \(p.616-617\)](#)



Agreements & certificates of conformity

- [QC / CB-FR_715099](#)



Installation & technical data

- [F00893EN-00](#)