

CAT. N° 0 955 07

**CABLE GLANDS METAL - IP68 - ISO 40 - CLAMPING CAPACITY 15-27 MM**

Pack (number of units)	5
Volume (dm <sup>3</sup> )	0,8
Weight (g)	567,00

**Product characteristics****Metal cable glands**

- Mechanically tightened cable glands with neoprene weatherproof seal for IP 68 protection.
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal mounted

**ISO**

- Conform to EN 50262
- ISO : 40
- Clamping capacity Ø Min. : 15 mm
- Clamping capacity Ø Max. : 27 mm

**General characteristics****Metal cable glands IP 68 - ISO and PG****Documentation****Catalogue pages & additional information**

- [Description page \(p.317\)](#)