

CAT. N° 0 955 08

**CABLE GLANDS METAL - IP68 - ISO 50 - CLAMPING CAPACITY 22-35 MM**

Pack (number of units)	2
Volume (dm ³)	0,843
Weight (g)	511,00

Product characteristics**Metal cable glands**

- Mechanically tightened cable glands with neoprene weatherproof seal for IP 68 protection.
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal mounted

ISO

- Conform to EN 50262
- ISO : 50
- Clamping capacity Ø Min. : 22 mm
- Clamping capacity Ø Max. : 35 mm

General characteristics**Metal cable glands IP 68 - ISO and PG****Documentation****Catalogue pages & additional information**

- [Description page \(p.317\)](#)