

CAT. N° 0 955 19

**CABLE GLANDS METAL - IP68 - PG 48 DIN - CLAMPING CAPACITY 35-48 MM**

Pack (number of units)	2
Volume (dm ³)	0,843
Weight (g)	588,00

Product characteristics**Metal cable glands**

- Mechanically tightened cable glands with neoprene weatherproof seal for IP 68 protection.
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal mounted

PG

- Conform to UTE C 68-300 and 68-312 guides recommendations
- PG : 48 DIN
- Clamping capacity Ø Min. : 35 mm
- Clamping capacity Ø Max. : 48 mm

General characteristics**Metal cable glands IP 68 - ISO and PG****Documentation****Catalogue pages & additional information**

- [Description page \(p.317\)](#)

**Environmental product profile**

- [LGRP-2014-115-V1-EN](#)