

CAT. N° 0 980 05

**CABLE GLAND PLASTIC - IP68 - ISO 25 - CLAMPING
CAPACITY 12-18 MM - RAL 7001**

Pack (number of units)	10
Volume (dm ³)	1,409
Weight (g)	302,00

Product characteristics**Grey RAL 7001 cable glands**

- Anti-vibration mechanically tightened cable gland with neoprene weatherproof seal for IP 68 protection
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal and locking nut mounted

ISO

- Conform to EN 50 262
- ISO : 25
- Clamping capacity Ø Min. : 12 mm
- Clamping capacity Ø Max. : 18 mm

General characteristics**Plastic cable glands IP 68 - ISO and PG****Documentation****Catalogue pages & additional information**

- [Description page \(p.316\)](#)

**Agreements & certificates of conformity**

- [VDE - 40010044](#)