

CAT. N° 0 980 07

**CABLE GLAND PLASTIC - IP68 - ISO 40 - CLAMPING
CAPACITY 22-32 MM - RAL 7001**

Pack (number of units)	3
Volume (dm ³)	1,408
Weight (g)	281,00

Product characteristics**Grey RAL 7001 cable glands**

- Anti-vibration mechanically tightened cable gland with neoprene weatherproof seal for IP 68 protection
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal and locking nut mounted

ISO

- Conform to EN 50 262
- ISO : 40
- Clamping capacity Ø Min. : 22 mm
- Clamping capacity Ø Max. : 32 mm

General characteristics**Plastic cable glands IP 68 - ISO and PG****Documentation****Catalogue pages & additional information**

- [Description page \(p.316\)](#)

**Agreements & certificates of conformity**

- [VDE - 40010044](#)