

CAT. N° 1 341 78



PRACTIBOX S FLUSH-MOUNTING CABINET FOR DRY PARTITION -EARTH + NEUTRAL TERMINAL BLOCKS -SMOKED DOOR -1 ROW -8 MODULES/ROW

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 6,641 |
| Weight (g) | 730,00 |

Product characteristics

Cabinets supplied with earth and neutral terminal blocks

- Smoked Transparent door
- Number of rows : 1
- Number of modules per row : 8
- Total number of modules : 8
- Height : 225 mm
- Width : 256 mm
- Depth : 100 mm

General characteristics

Practibox S - flush-mounting cabinets for dry partitions from 4 to 72 modules

- Allows to achieve assemblies conform to IEC 61439-3
- IP40 IK07
- Class II
- Plastic material
- Supplied with door
- For dry partitions
- 850° fireproof flush-mounting plastic boxes

Documentation

Catalogue pages & additional information

- [Description page \(p.217\)](#)
- [Technical page \(p.219\)](#)

Agreements & certificates of conformity

- [LOVAG - IT 18.173](#)
- [QC / CB - FR_703887/M1](#)

Installation instructions & related documents

- [LE10835AA_05](#)

Environmental product profile

- [Environnemental product sheet n°A E4067A-EN](#)