

CAT. N° 1 351 53



## PRACTIBOX S FLUSH-MOUNTING CABINET FOR MASONRY - EARTH + NEUTRAL TERMINAL BLOCKS - SMOKED DOOR - 3 ROWS - 12 MODULES/ROW

|                           |          |
|---------------------------|----------|
| Pack (number of units)    | 1        |
| Volume (dm <sup>3</sup> ) | 20,72    |
| Weight (g)                | 2 222,00 |

### Product characteristics

#### Cabinets supplied with earth and neutral terminal blocks

- Smoked Transparent door
- Number of rows : 3
- Number of modules per row : 12
- Total number of modules : 36
- Height : 535 mm
- Width : 328 mm
- Depth : 103 mm

### General characteristics

#### Practibox S - flush-mounting cabinets for masonry from 4 to 72 modules

- Allows to achieve assemblies conform to IEC 61439-3
- IP40 IK07
- Class II
- Plastic material
- Supplied with door
- For brick and masonry walls
- 650° fireproof flush-mounting plastic boxes

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.216\)](#)
- [Technical page \(p.219\)](#)

#### Installation & technical data

- [F02633EN-01](#)

#### Environmental product profile

- [Environnemental product sheet n°A E4067A-EN](#)

#### Installation instructions & related documents

- [LE10835AA\\_05](#)

#### Agreements & certificates of conformity

- [LOVAG - IT 18.173](#)
- [OC / CB - FR\\_703887/M1](#)