

REF . 1 370 08



PRACTIBOX S FLUSH-MOUNTING CABINET FOR MASONRY WITHOUT TERMINAL BLOCKS - WHITE DOOR - 3 ROWS WITH 18 MODULES PER ROW



Emballage (nombre number of units)	1
Volume (dm ³)	31,366
Poids (g)	2 732,00

Caractéristiques du produit

Cabinets supplied without terminal blocks

- White door
- Number of rows : 3
- Number of modules per row : 18
- Total number of modules : 54
- Height : 615 mm
- Width : 436 mm
- Depth : 103 mm

Caractéristiques générales

Practibox S - flush-mounting cabinets for masonry from 4 to 72 modules

- Allows to achieve assemblies conform to IEC 61439-3
- IP40 IK07
- Class II
- Plastic material
- Supplied with door
- For brick and masonry walls
- 650° fireproof flush-mounting plastic boxes

Documentation associée

Catalogue pages & additional information

- [Description page \(p.216\)](#)
- [Technical page \(p.219\)](#)

Installation & technical data

- [F02564EN-02](#)

Environmental product profile

- [LGRP-00539-V01](#)

Installation instructions & related documents

- [LE10835AA](#)

Agreements & certificates of conformity

- [LOVAG-IT 18](#)
- [OC / CB-FR_703887/M1](#)
- [LOVAG-IT 22](#)
- [LOVAG-IT 22](#)