

CAT. N° 1 370 55



PRACTIBOX S FLUSH-MOUNTING CABINET FOR MASONRY WITH EARTH TERMINAL BLOCKS - SMOKED DOOR - 1 ROW WITH 22 MODULES PER ROW

Pack (number of units)	1
Volume (dm ³)	14,036
Weight (g)	1 382,00

Product characteristics

Cabinets supplied with earth terminal blocks

- Smoked Transparent door
- Number of rows : 1
- Number of modules per row : 22
- Total number of modules : 22
- Height : 235 mm
- Width : 508 mm
- Depth : 102 mm

General characteristics

Practibox S - flush-mounting cabinets for masonry from 4 to 72 modules

- Allows to achieve assemblies conform to IEC 61439-3
- IP40 IK07
- Class II
- Plastic material
- Supplied with door
- For brick and masonry walls
- 650° fireproof flush-mounting plastic boxes

Documentation

Catalogue pages & additional information

- [Description page \(p.216\)](#)
- [Technical page \(p.219\)](#)

Installation & technical data

- [F02633EN-01](#)

Environmental product profile

- [LGRP-00899-V01](#)

Installation instructions & related documents

- [LE10835AA](#)

Agreements & certificates of conformity

- [LOVAG-IT 18](#)
- [OC / CB-FR_703887/M1](#)
- [LOVAG-IT 22](#)
- [LOVAG-IT 22](#)