

CAT. N° 2 811 23

**MULTISTANDARD SWITCHED SOCKET OUTLET WITH USB CHARGER MALLIA - 2 GANG - 2 X 2P+E - 16 A 250 V~ / 15 A 127 V~ - WHITE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,729
Weight (g)	211,00

**Product characteristics****Multistandard switched socket outlets 16 A - 250 V~ / 15 A - 127 V~ with USB charger**

- USB charger conform to IEC 60950-1

**2 x 2P+E - 2 gang**

- USB Type-A + Type-C™ 3 A - 5 VDC - 15 W
- Consumption in passive mode less than 0.08W
- White

**General characteristics****Mallia™ - multistandard and US standard socket outlets - complete white**

- Polycarbonate front cover plates with a matt finish
- Compact mechanism for greater wiring space
- Supplied with 2 screws M 3.5 for BS boxes
- All sockets integrate child protection
- Supplied complete with plate
- Dim.: 86 x 86 mm

**Documentation****Catalogue pages & additional information**

- [Description page \(p.566\)](#)

**Installation & technical data**

- [F02765EN-00](#)