

CAT. N° 282441-C2



## BRITISH STANDARD SOCKET OUTLET WITH USB TYPE-A CHARGER GALION - 13A 250V~ 1 GANG SINGLE POLE - SWITCHED - CHAMPAGNE

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### British Standard socket outlets 13 A - 250 V~ - with USB chargers

- Conform to BS 1363-2
- Consumption in passive mode

#### 1 gang single pole - switched, with USB charger Type-A

- 2.4 A - 5V= - 12W
- Champagne

### General characteristics

#### Galion™ - socket outlets

- Polycarbonate front cover plates
- Supplied with 2 screws M 3.5 for BS boxes
- Supplied complete with plate
- All sockets integrate child protection
- Dim.: 86 x 88mm (1 gang) ; 146 x 88mm (2 gang)

### Documentation



#### Installation & technical data

- [F03204EN-00](#)



#### Agreements & certificates of conformity

- [OC / CB-C-63 SE-88179M2](#)
- [OC / CB-FR-708240/M1](#)
- [OC / CB-SE-104797](#)
- [OC / CB-SE-101858](#)
- [G-MARK-LVE-2020-000862 V3](#)