

CAT. N° 282442-C2



MULTISTANDARD SOCKET OUTLET WITH USB TYPE-A CHARGER GALION - 16A 250V~ 1 GANG - SWITCHED - CHAMPAGNE

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Multistandard socket outlets 16 A - 250 V~ - with USB chargers

- Consumption in passive mode

1 gang - switched, with USB charger Type-A

- 2.4 A - 5V= - 12W
- Champagne

General characteristics

Galion™ - socket outlets, fused connection units and cable outlets

- Polycarbonate front cover plates
- Supplied with 2 screws M 3.5 for BS boxes
- Supplied complete with plate
- All sockets integrate child protection
- Dim.: 86 x 88mm (1 gang) ; 146 x 88mm (2 gang)

Documentation



Installation & technical data

- [F03025EN-01](#)