

CAT. N° 2 839 33



BRITISH STANDARD SOCKET OUTLET WITH USB CHARGER MALLIA - UNSWITCHED - 1 GANG - 13 A 250 V~ - CHAMPAGNE

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,426 |
| Weight (g) | 124,00 |

Product characteristics

British standard socket outlets - 13 A - 250 V~ with USB charger

- Conform to BS 1363-2
- USB charger conform to IEC 60950-1
- Supplied complete with plates

1 gang single pole unswitched

- USB Type-A 2.4 A - 5 VDC - 12 W
- Consumption in passive mode less than 0.08 W
- Champagne

General characteristics

Mallia™ - British standard socket outlets - customisable colours

- Painted polycarbonate front cover
- Compact mechanism for greater wiring space
- Supplied with 2 screws M 3.5 for BS boxes
- All sockets integrate child protection
- Dim.: 86 x 86 mm

Documentation

Catalogue pages & additional information

- [Description page \(p.572\)](#)

Agreements & certificates of conformity

- [OC / CB - SE-104796](#)
- [OC / CB - SE-101851](#)
- [OC / CB - SE-86036M1](#)

Installation & technical data

- [F02766EN-00](#)