

CAT. N° 3 101 25



## ON-LINE DOUBLE CONVERSION UPS - WITH ISOLATION TRANSFORMER - 3000 VA - 2400 W

Pack (number of units)	1
Volume (dm <sup>3</sup> )	306
Weight (g)	101 300,00

### Product characteristics

#### UPS with isolation transformer

- The stated backup time in minutes is estimated and may vary according to the load characteristics, operating conditions and environment
- Nominal power: : 3000 VA
- Active power: : 2400 W
- Backup time: : 10 min
- Weight: : 85 kg

### General characteristics

#### Keor S - On-line double conversion UPS (tower) - single phase

- For industrial environment (food industry, laboratories ...) or applications requiring long backup time (electro-medical ...)
- Installation: downstream power generators. Possibility to add batteries for extended autonomy. Parallel connection possible: up to 4 UPSs. Advanced management depending on the battery discharge level
- Sinusoidal output
- LCD screen
- Self-diagnosis
- Power factor: 0.9
- Integrated automatic bypass and maintenance bypass. Integrated slot for installing a communication interface for Ethernet network connection, to be ordered separately
- Cold Start Function. Microprocessor control
- Telephone line/Internet (RJ 11/RJ 45)
- Remote emergency shutdown function ("Emergency Power Off" - EPO). Equipped with 4 wheels for easy moving of the UPS

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.705\)](#)
- [Technical page \(p.706\)](#)



#### Installation & technical data

- [UPS\\_LGR\\_0087\\_GB\\_AA](#)