

CAT. N° 3 372 04



**XL<sup>3</sup> S 160 SURFACE-MOUNTING 24-MODULES PER ROW  
CABINET - RAL 9003 - 4 ROWS - 96 MODULES -  
740X595X135 MM**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	82,064
Weight (g)	14 626,00

**Product characteristics**

**Surface mounting 24-module per row cabinets**

- Faceplates and body: RAL 9003
- Number of rows : 4
- Number of modules : 96
- Height : 740 mm
- Width : 595 mm
- Depth : 135 mm

**General characteristics**

**XL<sup>3</sup> S 160 - 24 modules per row - "ready to use" metal distribution cabinets**

- Cabinets supplied with rails fitted (150 mm fixing centres) and full height faceplates
- Doors and terminal blocks to be ordered separately
- Take DPX<sup>3</sup> 160 and modular protection devices
- Used to create assemblies certified IEC 61439-2 and -3
- IP 40 with door
- IP 30 without door
- Cut-outs in top and bottom for feeding cables through
- Can take Lina 25 ducting

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.226\)](#)
- [Technical page \(p.229\)](#)

**Installation & technical data**

- [F02368EN-02](#)

**Installation instructions & related documents**

- [LE10065AE](#)

**Agreements & certificates of conformity**

- [LOVAG - IT 18.117](#)
- [LOVAG - IT 17.040](#)
- [LOVAG - IT 17.009](#)
- [LOVAG - IT 18.003](#)