

CAT. N° 3 372 07



## XL<sup>3</sup> S 160 SURFACE-MOUNTING 24-MODULES PER ROW CABINET - RAL 9003 - 7 ROWS - 168 MODULES - 1190X595X135 MM

Pack (number of units)	1
Volume (dm <sup>3</sup> )	123,984
Weight (g)	23 030,00

### Product characteristics

#### Surface mounting 24-module per row cabinets

- Faceplates and body: RAL 9003
- Number of rows : 7
- Number of modules : 168
- Height : 1190 mm
- Width : 595 mm
- Depth : 135 mm

### General characteristics

#### XL<sup>3</sup> S 160 - 24 modules per row - "ready to use" metal distribution cabinets

- Cabinets supplied with rails fitted (150 mm fixing centres) and full height faceplates
- Doors and terminal blocks to be ordered separately
- Take DPX<sup>3</sup> 160 and modular protection devices
- Used to create assemblies certified IEC 61439-2 and -3
- IP 40 with door
- IP 30 without door
- Cut-outs in top and bottom for feeding cables through
- Can take Lina 25 ducting

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.226\)](#)
- [Technical page \(p.229\)](#)

#### Installation & technical data

- [F02368EN-02](#)

#### Installation instructions & related documents

- [LE10065AE](#)

#### Agreements & certificates of conformity

- [LOVAG - IT 18.117](#)
- [LOVAG - IT 17.040](#)
- [LOVAG - IT 17.009](#)
- [LOVAG - IT 18.003](#)