

CAT. N° 3 375 30



**EXTERNAL CABLE SLEEVE FOR XL<sup>3</sup> S 630 ENCLOSURES**  
**-TOTAL HEIGHT 974 MM -FACEPLATE HEIGHT 900 MM**  
**-WIDTH 324 MM -DEPTH 249 MM**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	94,5
Weight (g)	17 280,00

## Product characteristics

### External cable sleeves

#### Side cable sleeves

- Fitted on either the right or left of enclosures using joining kits Cat.Nos 3 379 49/50
- Height total : 974 mm
- Height faceplate : 900 mm
- Width total : 324 mm
- Depth : 249 mm

## General characteristics

### XL<sup>3</sup> S 630 - distribution enclosures

- Enclosures equipped with functional uprights and supplied with fixing supports for faceplates (fixing accessories for faceplates to be ordered separately)
- Doors and side panels to be ordered separately
- Take protection devices up to 630 A
- Used to create assemblies certified IEC 61439-2
- IP 40 with door
- IP 30 without door
- Removable, separable top and bottom panels
- Can take Lina 25 ducting and IP 55 Cabstop cable gland plates

## Documentation

### Catalogue pages & additional information

- [Description page \(p.234\)](#)
- [Technical page \(p.254\)](#)

### Installation & technical data

- [F02369EN-01](#)

### Installation instructions & related documents

- [LE09457AE](#)

### Agreements & certificates of conformity

- [LOVAG - IT 17.083-R01](#)
- [LOVAG - IT 18.002](#)
- [LOVAG - IT 18.129](#)
- [LOVAG - IT 18.138](#)
- [LOVAG - IT 18.130](#)