

CAT. N° 3 375 60



**EXTERNAL CABLE SLEEVE FOR XL³ S 630 ENCLOSURES
-TOTAL HEIGHT 1424 MM -FACEPLATE HEIGHT 1350 MM
WIDTH 324 MM DEPTH 249 MM**

Pack (number of units)	1
Volume (dm ³)	141,858
Weight (g)	19 600,00

Product characteristics

External cable sleeves

Side cable sleeves

- Fitted on either the right or left of enclosures using joining kits Cat.Nos 3 379 49/50
- Height total : 1424 mm
- Height faceplate : 1350 mm
- Width total : 324 mm
- Depth : 249 mm

General characteristics

XL³ S 630 - distribution enclosures

- Enclosures equipped with functional uprights and supplied with fixing supports for faceplates (fixing accessories for faceplates to be ordered separately)
- Doors and side panels to be ordered separately
- Take protection devices up to 630 A
- Used to create assemblies certified IEC 61439-2
- IP 40 with door
- IP 30 without door
- Removable, separable top and bottom panels
- Can take Lina 25 ducting and IP 55 Cabstop cable gland plates

Documentation

Catalogue pages & additional information

- [Description page \(p.234\)](#)
- [Technical page \(p.254\)](#)

Installation & technical data

- [F02369EN-01](#)

Installation instructions & related documents

- [LE09457AE](#)

Agreements & certificates of conformity

- [LOVAG - IT 17.083-R01](#)
- [LOVAG - IT 18.002](#)
- [LOVAG - IT 18.129](#)
- [LOVAG - IT 18.138](#)
- [LOVAG - IT 18.130](#)