

CAT. N° 3 376 00



**EXTERNAL CABLE SLEEVE FOR XL<sup>3</sup> S 630 ENCLOSURES  
-TOTAL HEIGHT 2024 MM -FACEPLATE HEIGHT 1950 MM  
WIDTH 324 MM DEPTH 249 MM**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	193,725
Weight (g)	26 600,00

**Product characteristics**

**External cable sleeves**

**Side cable sleeves**


- Fitted on either the right or left of enclosures using joining kits Cat.Nos 3 379 49/50
- Height total : 2024 mm
- Height faceplate : 1950 mm
- Width total : 324 mm
- Depth : 249 mm

**General characteristics**

**XL<sup>3</sup> S 630 - distribution enclosures**

- Enclosures equipped with functional uprights and supplied with fixing supports for faceplates (fixing accessories for faceplates to be ordered separately)
- Doors and side panels to be ordered separately
- Take protection devices up to 630 A
- Used to create assemblies certified IEC 61439-2
- IP 40 with door
- IP 30 without door
- Removable, separable top and bottom panels
- Can take Lina 25 ducting and IP 55 Cabstop cable gland plates

**Documentation**

 **Catalogue pages & additional information**

- [Description page \(p.234\)](#)
- [Technical page \(p.254\)](#)

 **Installation & technical data**

- [F02369EN-01](#)

 **Installation instructions & related documents**

- [LE09457AE](#)

 **Agreements & certificates of conformity**

- [LOVAG - IT 18.130](#)
- [LOVAG - IT 17.083-R01](#)
- [LOVAG - IT 18.002](#)
- [LOVAG - IT 18.129](#)
- [LOVAG - IT 18.138](#)