

CAT. N° 3 376 01



## XL<sup>3</sup> S 630 DISTRIBUTION ENCLOSURES WITH 16 MODULES WIDE - TOTAL 2024X454X249 MM AND USABLE 1950X350X249 MM

Pack (number of units)	1
Volume (dm <sup>3</sup> )	249,075
Weight (g)	35 500,00

### Product characteristics

#### Enclosures

##### 16 modules wide

- Faceplates: RAL 9003
- Body: RAL 7016
- Height total : 2024 mm
- Height faceplate : 1950 mm
- Width total : 454 mm
- Width usable : 350 mm
- Depth : 249 mm

### General characteristics

#### XL<sup>3</sup> S 630 - distribution enclosures

- Enclosures equipped with functional uprights and supplied with fixing supports for faceplates (fixing accessories for faceplates to be ordered separately)
- Doors and side panels to be ordered separately
- Take protection devices up to 630 A
- Used to create assemblies certified IEC 61439-2
- IP 40 with door
- IP 30 without door
- Removable, separable top and bottom panels
- Can take Lina 25 ducting and IP 55 Cabstop cable gland plates

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.234\)](#)
- [Technical page \(p.254\)](#)

#### Agreements & certificates of conformity

- [LOVAG-IT 17](#)
- [LOVAG-IT 18](#)
- [LOVAG-IT 18](#)
- [LOVAG-IT 18](#)
- [LOVAG-IT 18](#)

#### Installation & technical data

- [F02369EN-01](#)

#### Environmental product profile

- [LGRP-00471-V01](#)