

CAT. N° 3 379 35



## INTERNAL CABLE SLEEVE KIT FOR XL<sup>3</sup> S 630 ENCLOSURES - TOTAL HEIGHT 1274 MM AND FACEPLATE HEIGHT 1200 MM

Pack (number of units)	1
Volume (dm <sup>3</sup> )	8,728
Weight (g)	5 215,00

### Product characteristics

#### Internal cable sleeves

##### Internal cable sleeve kits

- For mounting on either the right or left inside XL<sup>3</sup> S 630 enclosures
- Height total : 1274 mm
- Height faceplate : 1200 mm

### General characteristics

#### XL<sup>3</sup> S 630 - distribution enclosures

- Enclosures equipped with functional uprights and supplied with fixing supports for faceplates (fixing accessories for faceplates to be ordered separately)
- Doors and side panels to be ordered separately
- Take protection devices up to 630 A
- Used to create assemblies certified IEC 61439-2
- IP 40 with door
- IP 30 without door
- Removable, separable top and bottom panels
- Can take Lina 25 ducting and IP 55 Cabstop cable gland plates

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.234\)](#)
- [Technical page \(p.254\)](#)

#### Agreements & certificates of conformity

- [LOVAG-IT 17](#)
- [LOVAG-IT 18](#)
- [LOVAG-IT 18](#)
- [LOVAG-IT 18](#)
- [LOVAG-IT 18](#)

#### Installation instructions & related documents

- [LE09898AA](#)

#### Environmental product profile

- [LGRP-00471-V01](#)