

CAT. N° 3 381 02



## METAL DOOR FOR XL<sup>3</sup> S 4000 DISTRIBUTION ENCLOSURES HEIGHT 2000 MM AND WIDTH 600 MM - SUPPLIED WITH FIXED HANDLE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	157,954
Weight (g)	18 636,00

### Product characteristics

#### Metal doors

- Supplied with fixed handle

#### Height 2000 mm

- For enclosure width : 600 mm

### General characteristics

#### XL<sup>3</sup> S 4000 - distribution enclosures and equipment

- Doors, side or rear panels, supports for faceplates and functional uprights, to be ordered separately
- Enclosures supplied with corner pieces for plinth
- Take protection devices up to 4000 A
- Used to create assemblies certified IEC 61439-2
- IP 30 without door
- IP 40 with door
- External height 2000 or 2200 mm
- Capacity 16 modules/row (424 mm wide enclosures), 24 modules/row (574 mm or 800 mm wide enclosures with internal cable sleeve), 36 modules/row (774 mm wide enclosures)
- Usable faceplate height 1800 mm or 2000 mm

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.246\)](#)
- [Technical page \(p.255\)](#)

#### Agreements & certificates of conformity

- [LOVAG - IT 18.039](#)
- [LOVAG - IT 17.096](#)
- [LOVAG - IT 18.038](#)
- [LOVAG - IT 18.047](#)
- [LOVAG - IT 18.118](#)
- [LOVAG - IT 18.001](#)

#### Installation instructions & related documents

- [LE09702AB](#)