

CAT. N° 3 382 71



## WINDOW FACEPLATES FOR XL<sup>3</sup> S 630 AND 4000 16-MODULE ENCLOSURES - HEIGHT 300 MM FOR DPX<sup>3</sup> 160/250 AND DPX-IS 250

Pack (number of units)	1
Volume (dm <sup>3</sup> )	2,433
Weight (g)	1 020,00

### Product characteristics

#### Faceplates for DPX-IS 250 - vertical mounting

- Fixed with locking clips, 1/4 turn screws or screws

#### Height 300 mm

- For 16-module enclosure

### General characteristics

#### XL<sup>3</sup> S 4000 - equipment for mounting DPX-IS 250 on plate

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.230-231\)](#)
- [Selection chart \(p.232-233\)](#)
- [Description page \(p.237\)](#)
- [Description page \(p.238\)](#)
- [Selection chart \(p.242-243\)](#)
- [Description page \(p.248\)](#)
- [Description page \(p.249\)](#)
- [Technical page \(p.254\)](#)

#### Agreements & certificates of conformity

- [LOVAG - IT 17.083-R01](#)
- [LOVAG - IT 18.002](#)
- [LOVAG - IT 18.039](#)
- [LOVAG - IT 17.096](#)
- [LOVAG - IT 18.038](#)
- [LOVAG - IT 18.047](#)
- [LOVAG - IT 18.137](#)
- [LOVAG - IT 18.001](#)